

ZERUST®/EXCOR® Axxatec™ 48C is a water-based rust preventative liquid concentrate for the protection of ferrous, aluminum, and yellow metals for up to 6 months<sup>‡</sup> during indoor storage, shipping, and assembly. Applied at 3 – 10% dilution, it leaves a clear, dry-to-touch protective coating after drying. As a result, it's safer and more economical to use than solvent-based systems. Axxatec™ 48C does not contain solvent, is non-flammable, meets Global Automotive Declarable Substance, TSCA, ECHA SVHC, RoHS, and REACH requirements, and is environmentally friendly.

## **Typical Properties**

Appearance Clear pale yellow water-like liquid

Surface finish

Substrates

VOC content EPA Method 24 (concentrate)

Freeze point

Clear, dry-to-touch

Multimetal protection

No volatile organic content

21°F (-6°C)

pH (concentrate) 9 – 10 pH (5% solution) 9 – 10

This data sheet provides general guidelines for operation, application, and removal. Please contact your ZERUST®/EXCOR® account representative for more specific recommendations on your particular operation and conditions.

## **Operating Summary**

- Diluted between 3 10% in water.
- Typical operating temperature: ≥72°F (22°C) in most operations.
- Deionized or reverse osmosis water is required for bath makeup and rinsing to improve bath life and reduce corrosion
  potential, as the product is not hard water compatible.
- Dry well after application.

# Application Technologies

• Can be used in immersion or hand spray processes.

#### **Product Removal**

Axxatec<sup>™</sup> 48C is designed to be left on the metal surface as a rust preventative product. However, it can be rinsed and
removed from the metal surface with the use of compatible ZERUST® AxxaWash™ products, or contact your ZERUST®/EXCOR®
account representative for more specific removal recommendations on your particular operation and conditions.

#### **Product Control**

Axxatec<sup>™</sup> 48C is controlled by titration. To test the concentration:

- Pipette a 20 mL sample of the bath solution into a beaker.
- Add 50 mLs of DI, RO, or distilled water.
- Add 10 drops of bromocresol green indicator solution. The solution should turn green.
- Titrate with 0.1 N hydrochloric or sulfuric acid until the color turns yellow.
- Use the following table to determine concentration.

% Axxatec <sup>™</sup> 48C	Titrant Volume (mLs)
1	1.3
3	3.3
5	5.2
7	7.1
9	9.1



## **Availability**

ZERUST®/EXCOR® Axxatec™ 48C is sold as a liquid concentration. Contact your ZERUST®/EXCOR® representative for ordering information.

Part Number	Quantity*
350-M-00097PL	5 Gal (19 L) Pail
350-M-00097DR	55 Gal (208 L) Drum
350-M-00097TT	275 Gal (1041 L) Tote

<sup>\*</sup>Product sold in US customary units. Metric units approximate.

#### Protection Info<sup>‡</sup>

Indoor (unpackaged)<sup>‡</sup> Up to 6 months<sup>‡</sup> Indoor (w/ VCI packaging)<sup>‡</sup> For years<sup>‡</sup>

Outdoor<sup>‡</sup> Not recommended

Compatible with packaging Yes

## **Storage**

- Store in a cool, dry place and away from sunlight in the original packaging.
- Optimal storage temperature is 40 100°F (4 38°C) for up to 2 years from the date of shipment.
- If the product freezes, bring it to room temperature and mix well.
- Reseal or close the container cap after each use.

## **Disposal**

- Dispose of in accordance with local, national, and international regulations.
- Product in an unopened original container prior to use does not meet criteria for hazardous waste according to 40 CFR 261 (no components listed on F, K, P, or U lists; not ignitable, not corrosive, not reactive, and not toxic).

#### **Precautions**

- Product foams when used in pressurized spray applications. Contact your ZERUST®/EXCOR® representative for recommendations for suitable defoaming agents.
- Always mix well before use.
- Deionized or reverse osmosis water is recommended for bath makeup and rinsing to improve bath life and reduce corrosion potential.
- Avoid contact with eyes and skin.
- Provide adequate ventilation and minimize exposure to vapors.
- Do not breathe mist, spray, or vapors.
- Wear personal protective equipment as stipulated in Safety Data Sheet (SDS).
- Refer to SDS for more safety information.

#### ‡ DECLARATION

Corrosion protection claims are based on Northern Technologies International Corporation (NTIC) internal laboratory testing performed under controlled parameters on contaminate-free substrates. Real-world application corrosion protection duration on different substrates will vary and depends on factors such as, but not limited to, the application or use, environmental / storage conditions, surface cleanliness, type of substrates, and coating thickness (where applicable). The use of the term "Up to" in reference to time is defined as any time duration from zero up to a specified time frame, but in no event beyond the specified time frame. The use of the term "for years" is based on NTIC's experience with its products but is in no way guaranteed. The use of the term "Up to" in reference to volume is defined as any volume from zero up to a specified volume but in no event beyond the specified volume of protection. It is the customer's / user's obligation to evaluate product performance, corrosion protection duration, safety, and suitability for intended use within the scope advised in the data sheet and to comply with all applicable laws and regulations. LIMITED WARRANTY/DISCLAIMER Warranty is limited to the replacement of a product that fails to meet specifications. For full warranty and disclaimer information, visit www.zerust.com/warranty.

©2013-2023 Northern Technologies International Corporation (NTIC). All Rights Reserved. NTIC is the owner of the following trademarks: ActivPak®, Cor Tab®, EXCOR®, Flange Saver®, ICT®, Natur-VCI®, NTI®, Plastabs®, Z-CIS®, Zerion®, ZERUST®, 洁乐特, Z-PAK® and the Color "Yellow". ABRIGO®, UNICO®, and VALENO® are registered trademarks of EXCOR GmbH, a Joint Venture Partner of NTIC.

A product of: Northern Technologies International Corp 4201 Woodland Road Circle Pines, MN 55014

Phone. +1 763.225.6600 Fax. +1 763.225.6645 sales@zerust.com www.zerust.com

Rev A

